


RXTi2

INDUCTION LOOP RECEIVER

part of the ((soundfields)) range



The RXTi2 Induction Loop Receiver picks up audio signals from the loop through a pair of headphones (not supplied) and allows the signal quality to be assessed for testing purposes.

Designed to allow installers and the non hard of hearing to test and assess the quality and availability of a loop system. The RXTi2 may also be used in non hard of hearing applications such as multi-lingual translations, museum talk-through systems and stage talk-back systems.

features

- Soft start function
- 50Hz filter (to cut out mains hum pick up)
- Compact size
- 3.5mm headphone socket (for headset / earbud)
- Powered by 2 x AAA batteries

CAUTION: The audio output from the RXTi2 can exceed 100mW into 8Ω. This may cause hearing damage with long term exposure. Care should be taken not to use excessive volume when testing loop systems

